



**DX6 MX** Digitally enabled powder-actuated tool for fastening collated nails

**Fastener guide:**

X-6-MX72

**Fastener:**

X-X\_MX

X-P\_MX

X-U\_MX

X-C\_MX

X-CT\_MX

X-FS\_MX

X-SW\_MX

X-ET\_MX

X-ECT\_MX

X-EKS\_MX

X-FB\_MX

X-HS\_MX

X-HS-W\_MX

X-ECC\_MX

X-ECH\_MX

X-EKB\_MX

**Piston:**

X-6-5-P8

X-6-5-P8W

for wood fastening

**Cartridge:**

6.8/11 M 10 for DX 6

titanium, black

**DX6 F8** Digitally enabled powder-actuated tool for fastening single nails



Standard fastener guide

**Fastener guide:**

X-6-F8



**Fastener:**

X-X\_P8

X-P\_P8

X-U\_P8

X-U\_P8 TH

X-C\_P8

X-CR\_P8

X-CR\_P8S12

X-CR M8

X-R\_P8

X-ST-GR M8\_P8

X-CT\_DP8

X-FS

X-DFS

X-SW

X-FB

X-EM6H-\_FP8

X-EW6H-\_FP8

X-EF7H-\_FP8

X-M6-\_FP8

X-W6-\_FP8

X-F7-\_FP8

X-EM8H-\_P8

X-M8-\_P8

X-HS

X-CC

X-HS-W\_P8

**Piston:**

X-6-5-P8

X-6-5-P8W

for wood fastening

X-6-5-P8AL

**Cartridge:**

6.8/11 M 10 for DX 6

titanium, black

**DX-Kwik fastener guide (DX-Kwik method/pre-drilled concrete)**
**Fastener guide:**

X-6-F8


**Fastener:**

X-M6H-\_-37 FP8

X-M8H-\_-37 P8

X-CRM8-\_-42

**Piston:**

X-6-5-PKwik

**Cartridge:**

6.8/11 M10 for DX 6  
titanium, black

**Fastener:**

X-DNH 37 P8S15

X-DKH 48 P8S15

**Piston:**

X-6-5-P8

**Cartridge:**

6.8/11 M10 for DX 6  
titanium, black

**Narrow access fastener guide (Ø: 15.2 mm, h: 53.2 mm)**
**Fastener guide:**

X-6-F8N15


**Fastener:**

X-P\_P8

X-U\_P8

X-C\_P8

X-CR\_P8

X-CRM\_P8

X-ST-GR M8\_P8

**Piston:**

X-6-5-P8

**Cartridge:**

6.8/11 M10 for DX 6  
titanium, black

**Narrow access fastener guide (w × t × h: 10.4 × 25.9 × 50 mm)**
**Fastener guide:**

X-6-F8N10


**Fastener:**

X-P\_P8

X-U\_P8

X-C\_P8

X-CR\_P8

X-CRM\_P8

**Piston:**

X-6-5-P8

**Cartridge:**

6.8/11 M10 for DX 6  
titanium, black

## Grating fastener guide

**Fastener guide:**

X-6-FGR


**Fastener:**

 X-GR  
 X-PGR-RU  
 X-ST-\_M8\_P8  
 X-EM 8H

**Piston:**

X-6-5-PGR

**Cartridge:**

 6.8/11 M10 for DX 6  
 titanium, black

## M10 fastener guide

**Fastener guide:**

X-6-5-F10


**Fastener:**

 DS\_P10  
 EDS 19 P10, EDS 22 P10  
 X-EM8H-15-12 FP10  
 X-EM10H-24-12 P10

**Piston:**

X-6-5-P10

**Cartridge:**

 6.8/11 M10 for DX 6  
 titanium, black

## Insulation fastener guide (up to 140 mm insulation thickness)

**Fastener guide:**

X-6-FIE-L


**Fastener:**

 X-IE  
 XI-FV

**Piston:**

X-6-5-PIE-L

**Cartridge:**

 6.8/11 M10 for DX 6  
 titanium

## Insulation fastener guide (up to 200 mm insulation thickness)

**Fastener guide:**

X-6-FIE-XL


**Fastener:**

 X-IE  
 XI-FV

**Piston:**

X-6-5-PIE-XL

**Cartridge:**

 6.8/11 M10 for DX 6  
 titanium

**DX6 IE** Digitally enabled powder-actuated tool for fastening insulation

**Fastener guide:**

X-6-FIE-XL

**Fastener:**

X-IE

XI-FV

**Piston:**

X-6-5-PIE-XL


**Cartridge:**

6.8/11 M10 for DX 6  
titanium

**DX6 GR** Digitally enabled powder-actuated tool for fastening grating

**Fastener guide:**

X-6-FGR

**Fastener:**

X-GR

X-PGR-RU

X-EM 8H

**Piston:**

X-6-5-PGR


**Cartridge:**

6.8/11 M10 for DX 6  
titanium, black

**DX6 F10** Digitally enabled powder-actuated tool

**Fastener guide:**

X-6-F10

**Fastener:**

DS\_P10

EDS 19 P10, EDS 22 P10

X-EM8H-15-12 FP10

X-EM10H-24-12 P10

**Piston:**

X-6-5-P10


**Cartridge:**

6.8/11 M10 for DX 6  
titanium, black